Model BD 720 | Incubators Classic.Line with natural convection

BENEFITS

- · Safe and reproducible incubation even under high batch throughputs in long-term operation
- Disinfection routine at 100 °C
- · Stable atmosphere by inner glass door



MAIN FEATURES

- Temperature range: room temperature plus 5 °C to 100 °C
- APT.line[™] preheating chamber technology
- Free convection
- Adjustable exhaust air flap
- Controller with timer functions
- Inner door made of tempered safety glass
- · 2 chrome-plated racks
- Class 3.1 independent temperature safety device (DIN 12880) with visual temperature alarm
- Computer interface: RS 422

ORDERING INFORMATION

Interior volume [L]	Voltage	Option model	Version	ArtNo.
Model BD 720				
700	230 V 1~ 50/60 Hz	Standard	BD720-230V	9010-0074
720	120 V 1~ 60 Hz	0 Hz Standard BD720UL-120V	9010-0177	

TECHNICAL DATA

Description	BD720-230V	BD720UL-120V
Article Number	9010-0074	9010-0177
Performance Data Temperature		
Temperature range 5 °C above ambient temperature to [°C]	100	100
Temperature variation at 37 °C [± K]	0.5	0.5
Temperature fluctuation at 37 °C [± K]	0.1	0.1
Heating-up time to 37 °C [min]	110	110
Recovery time after 30 seconds door open at 37 °C [min]	15	15

Description	BD720-230V	BD720UL-120V
•		
Article Number	9010-0074	9010-0177
Electrical data		
Rated Voltage [V]	230	120
Power frequency [Hz]	50/60	60
Nominal power [kW]	1.25	1.25
Unit fuse [A]	16	16
Phase (Nominal voltage)	1~	1~
Measures - Outer dimensions		
Width net [mm]	1235	1235
Height net [mm]	1530	1530
Depth net [mm]	865	865
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Measures - Doors		
Unit doors	2	2
Measures - Internal Dimensions		
Width [mm]	1000	1000
Height [mm]	1200	1200
Depth [mm]	600	600
Measures		
Interior volume [L]	720	720
Net weight of the unit (empty) [kg]	191	191
permitted load [kg]	120	120
Load per rack [kg]	45	45
Environment-specific data		
Energy consumption at 37 °C	80 Wh/h	80 Wh/h
Fixtures		
Number of shelves (standard/maximum)	2/15	2/15

OPTIONS AND ACCESSORIES

Designation	Description	*	ArtNo.
	10 mm, back	01	8012-0390
	10 mm, left	01	8012-0388
	10 mm, right	01	8012-0387
	10 mm, top	01	8012-0386
	30 mm, back	01	8012-0397
	30 mm, left	01	8012-0047
Access port with silicone plug	30 mm, right	01	8012-0046
jidg	30 mm, top	01	8012-0045
	50 mm, back	01	8012-0399
	50 mm, left	01	8012-0051
	50 mm, right	01	8012-0050
	50 mm, top	01	8012-0049
	100 mm, top	01, 10	8012-0053
Analog output, 4 – 20 mA	for temperature values (output not adjustable)	-	8012-0432
Calibration certificate, expanded	each measurement at additional measuring point or testing temperature	_	8012-0022

* Notes > See last page

Designation	Description	*	ArtNo.
	for temperature, measurement in center of chamber at specified temperature	-	8012-0030
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-0921
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-0918
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-0915
Data Logger Kit	T 220: temperature logging from -90 °C to 220 °C	19	8012-0715
Data Logger Kit, software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-0821
Door lock	lockable door handle	-	8012-0319
	RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-0557
	230 V, 50/60 Hz option model	-	8012-0556
Interface converter	RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-040
	230 V, 50/60 Hz option model	-	8012-0380
Interface converter, USB / RS422	RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection to a unit (USB-powered converter)	-	8012-066
Interior socket	coverable, with associated LEMO connector (nominal voltage, max. 500 W, max. 90 °C, protection class IP67)	07	8012-007
Magnetic Pouch (A4)	insert pouch with magnetic strip	-	1007-006
	audible, can be switched off, adjustable limit on the independent temperature safety device		
Overheating alarm	120 V, 208 V option model	-	8012-047
	230 V, 400 V option model	-	8012-046
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-001
Pt 100 temperature sensor	additional Pt 100, with flexible cable installed with external connection, incl. LEMO connector (3-pin)	-	8012-011
5 .	chrome plated	-	6004-0006
Rack	stainless steel	-	6004-0010
RS 422 interface	modular plug distributor for 10 RS 422 interfaces	-	8012-029
RS 422 interface, cable (15 m)	RS 422 connection cable (15 m) between plug distributor and RS 422 interface	-	5023-003
RS 422 interface, cable (50 m)	RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor	-	5023-011
Rubber pads	set of 4 anti-slip feet, for safe stacking of unit	10	8012-000
Shelf, perforated	stainless steel	-	6004-003
	APT-COM™ communications software		
Software	version 2 to 3, GLP edition	19	9053-001
	version 3, BASIC edition	19	9053-001
	version 3, GLP edition	19	9053-001
	version 3, STANDARD edition	19	9053-001
	APT-COM™ communications software, price: for free		
	version 3, GLP DEMO Edition	19	9053-000

* Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL100100
Instruction	unit function instructions for operation and programming of the controller	18	DL100400
Preventive maintenance			
Preventive maintenance	Executive of equipment inspection according to maintenance plan	14, 18	DL200200
* Notos > Soo last page			

* Notes > See last page

Data Sheet Model BD 720

Designation	Description	*	ArtNo.
Calibration services			
Calibration temperature	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL300101
Temperature measurement 18 measuring points	including certificate, 18 measuring points at specified temperature	14, 16, 17, 18	DL300118
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL300127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL300109
Validation services			
Execution of IQ/OQ	in accordance with qualification folder	15, 18, 20	DL400100
Execution of IQ/OQ/PQ	in accordance with customer's requirement, price: on request	15, 18	DL440500
Qualification folder IQ/OQ	supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001	15, 18, 20	8012-0870
Qualification folder IQ/OQ/PQ	supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ	15, 18	8012-0958
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	-	DL016041
Extension of the warranty from 2 to 5 years	beginning with the date of delivery, wearing parts are not included	-	DL016042

* Notes > See last page

NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used. 01
- 02
- Heat resistant only to max. 200 °C. 03 Only available on units rated for 230 V. 04
- 06
- Heating-up time may increase as a result of the lower heat conductivity. 07 The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting. 09
- 10 11 12 Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract (see the chapter on BINDER Service) to cover unit inspections, calibrations and validations
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory. 16
- Calibration is performed according to the BINDER factory standard. 17
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not 18 include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter. 19
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.
- When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder. 21
- ATEX conformity: Pumping chamber (pumped gases): II 2G IIC T3 X Environment with inert purge gas: II 2G IIB T4 X Environment without inert purge gas: II 3G IIB T4 X Motor: II 2G Ex d IIB T4 Gb

BINDER GmbH Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd. Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

BINDER Environmental Testing Equipment (Shanghai) Co., Ltd. Shangha, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS Moscow. Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.ru

BINDER Inc. Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us